

# MilSight™ T90 TaNS®

TACTICAL NIGHT SIGHT



*MilSight T90 TaNS (Tactical Night Sight) on M4*

## APPLICATIONS

TARGET ACQUISITION

RECONNAISSANCE

COVERT OPERATIONS

SURVEILLANCE

SPECIAL LAW ENFORCEMENT

## FEATURES

Compatible with Standard Sight

Multi-use design

Optimized for close combat assault rifles

Built-in image intensifier protection for added longevity

Small and lightweight

Simple operation

No special batteries required

It's all FLIR inside

## BENEFITS

Designed to mount on any MIL-STD-1913 rail interface forward of an existing scope, adding blended thermal and night vision capabilities to daytime target acquisition platforms

Offers mission flexibility as a high-resolution night vision weapon sight, mounted on a spotting scope for long range reconnaissance, hand-held as an observation device, or used in other night-time operations requiring night vision capabilities

Effective on all weapons from carbines to .50 caliber bolt action rifles, including the M4, M16, HK416, and the AK47

Includes FLIR's proprietary Shock Mitigation System™ (SMS™), allowing the unit to be used on weapons up to and including .50 caliber bolt-action rifles

Highly portable design reduces operator fatigue

Large, rugged controls for basic image adjustment, no complicated menus to navigate

Runs on common AA batteries

FLIR controls the entire supply chain on the critical technology inside the UNS sight ensuring fast service and long term support



## MilSight™ T90 TaNS®

### SYSTEM CHARACTERISTICS

Magnification	Unity
Optimum Dayscope Magnification	1x to 8x
Focus Range	3 m to Infinity
Field of View	14h°
Image Intensifier Gain	1,000 – 75,000

### BORESIGHT CHARACTERISTICS (REFERENCES I2 & IR CHANNELS)

Accuracy	Factory Aligned to ½ MOA or Better
Adjustments	None
Repeatability	Within ½ MOA

### PHYSICAL CHARACTERISTICS

Shock Mitigation System™ (SMS™)	
Operating Temperature	-30° to +60° C
Submersion	66 ft. for 2 hours
Interface (to MIL-STD 1913)	Single Adjustable Locking Lever Mount

### POWER

Power requirements	AA or CR123
--------------------	-------------

### DIMENSIONS, WEIGHT & MOUNTING

Interface (to MIL-STD 1913)	Single Locking Lever
Length	5.6"
Weight (w/o batteries)	24 oz
Max Height Above Rail	3.05"

### INTERFACES

Command and Control	On/Off/Gain, Focus
---------------------	--------------------

### PERFORMANCE

Resolution (Minimum)	2.5 cy/mr
Resolution (Typical)	2.9 cy/mr

### FACIAL ID RANGES

Starlight, Low Contrast	65 m
Starlight, Optimum Contrast	90 m
¼ Moonlight, Low Contrast	90 m
¼ Moonlight, Optimum Contrast	105 m

### MAN DETECTION RANGES

Starlight, Low Contrast	640 m
Starlight, Optimum Contrast	880 m
¼ Moonlight, Low Contrast	880 m
¼ Moonlight, Optimum Contrast	1070 m

### OPTICAL CHARACTERISTICS

Objective Lens Focal Length	50 mm
Objective Lens f/Number	f/0.9
Output Optic Exit Pupil Diameter	33 mm

### CORPORATE HEADQUARTERS

FLIR Systems, Inc.  
27700 SW Parkway Ave.  
Wilsonville, OR 97070  
PH: +1 800.727.3547

### BOSTON

FLIR Systems, Inc.  
25 Esquire Road  
North Billerica, MA 01862  
PH: +1 800.464.6372

### HUNTSVILLE

FLIR Systems, Inc.  
Huntsville, AL USA  
PH: +1 256.325.3547

### PITTSBURGH

FLIR Systems, Inc.  
Freeport, PA USA  
PH: +1.724.295.2880

### WASHINGTON, D.C.

FLIR Systems, Inc.  
2800 Crystal Drive, Suite 330  
Arlington, VA 22202 USA  
PH: +1 703.416.6666

### EUROPE

FLIR Systems Ltd.  
West Malling, Kent  
United Kingdom  
PH: +44.1732.220011

### CANADA

FLIR Systems Ltd.  
Burlington, ON  
Canada  
PH: +1 800.613.0507

### SWEDEN

FLIR Systems AB  
Täby, Sweden  
PH: +46.8.753.2500

### MIDDLE EAST

FLIR Systems Middle East, FZCO  
Dubai Airport Free Zone  
PH: +9714.299.6898

[www.flir.com/GS](http://www.flir.com/GS)

